



# **HSM Crusher 1049 SA**

## **HSM PET-Crusher 1049 SA**

As a result of the HSM solution, the space required for returned empties is reduced to approx. 25-30 % of the original volume and as such, also reduces the time required for disposal. The special roller system perforates and crushes the containers. The sidewalls mesh into each other, making the reduction in volume permanent. Crushing has an additional advantage: deposit plastic bottles and cans are reliably invalidated.

## **Technical data**

Order number:	1692103	Contain
EAN	4026631048019	collecti
Driving power:	2.01 HP	Through
Voltage / Frequency:	110 V / 60 Hz	Width x
Working width:	19.29"	Weight:
Loading height:	47.5"	Press m

Container volume / collecting:	76.6 gal
Throughput (1l bottle/h):	2000
Width x Depth x Height:	31.22" x 68.94" x 80.2"
Weight:	525.58 lb
Press material:	PET, PET beverage and aluminium cans, soft


# **Product information**



An efficient system for the volume reduction of PET bottles and cans down to 1/3 or 1/4 of the original



Throughput per hour up to 2400 PET bottles (1 litre)



packaging

The cutting head can also be used in combination with a deposit return machine





#### **Durable and robust**

Crusher rollers made of specially hardened and ground steel, completely resistant to wear and very strong, for a long service life.



#### **Energy saving**

Automatic switch off after two minutes to save energy – available for continuous operation.



## Keypad

Manual control of the machine via easy-to-use keypad with forward, reverse and stop functions.



# **LED display**

LED display provides information on the current status of the machine (ready, overload, door open, container full).



# **Dosing shaft**

A dosing shaft with integrated blades ensures that the plastic bottles and cans are fed reliably.



### **Scraper system**

A scraper system removes the compressed plastic bottles and cans from the crusher rollers to prevent blockages and downtime while clearing.

